



3031

## Rocker switch off, Module inserts

### Technical characteristics

#### Architecture

Type of control unit single rocker

#### Configuration

Switch mode Off

Antibacterial treatment No

#### Compatibility

IFTTT support available No

#### Controls and indicators

Push-buttons No

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

#### Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

#### Dimensions

Depth 41.6 mm

Insertion depth 31 mm

Height 70.8 mm

Width 70.8 mm

#### Materials

Surface appearance other

#### Installation, mounting

Installation mode with spreader claws ; for screw fastening

#### Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Type of connection Quickconnect

#### Equipment

Lighting for lighting and monitoring circuit

Heating switch	No
----------------	----

---

**Use cases**

Application	Light control
-------------	---------------

---

**Safety**

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

Impact strength	IK07
-----------------	------

---

**Identification**

Application, usage	Light control
--------------------	---------------

Main design line	Light control
------------------	---------------