



303212

## On/off switch 2pole 16 AX, light control

### Technical characteristics

#### Architecture

Type of control unit single rocker

#### Configuration

Switch mode 2-pole off ; with predefined neutral position

Antibacterial treatment No

#### Compatibility

IFTTT support available No

#### Controls and indicators

Push-buttons No

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

#### Electric current

Switching current 16 AX (200 W Self Ballasted Lamp (SBL))

#### Dimensions

Depth 42 mm

Insertion depth 32 mm

Height 71 mm

Width 71 mm

#### Materials

Surface appearance matt

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with screw terminals

Type of connection Screw connection

#### Equipment

Lighting for lighting and monitoring circuit

Heating switch No

---

**Use cases**

Application Light control

---

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free No

Impact strength IK07

---

**Identification**

Appliance switch type No

Main design line Light control

---

**Instructions**

Information text

spreader claws, insulated to the supporting ring, self-resetting ; Only suitable in combination with rockers with "0" imprint.