



303303

On/off switch 3pole 16A/400V

Technical characteristics

Architecture

Type of control unit single rocker

Configuration

Switch mode 3-pole off ; with predefined neutral position

Antibacterial treatment No

Compatibility

IFTTT support available No

Controls and indicators

Push-buttons No

Main electrical features

Nominal voltage 400 V

Rated voltage 400 V AC

Electric current

Switching current 16 A

Dimensions

Depth 42 mm

Insertion depth 31 mm

Height 71 mm

Width 71 mm

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with screw terminals

Type of connection Screw connection

Equipment

Lighting for lighting and monitoring circuit

Heating switch No

Use cases

Application Light control

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK05

Identification

Application, usage	HVAC control ; Light control
Main design line	Light control

Instructions

Information text	spreader claws, insulated to the supporting ring, self-resetting ; Only suitable in combination with rockers with "0" imprint.
------------------	--