



303303

On/off switch 3pole 16A/400V

Technical characteristics

Architecture

Type of control unit	single rocker
Fixing mode	flush-mounting

Configuration

Switch mode	3-pole off, with predefined neutral position
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Nominal voltage	400 V
Rated voltage	400 V AC

Electric current

Switching current	16 A
-------------------	------

Dimensions

Depth	42 mm
Insertion depth	31 mm
Height	71 mm
Width	71 mm

Materials

Material	Plastic/metal
----------	---------------

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60669-1
Connection terminals	according to VDE 0632-1
Type of connection	with screw terminals
Type of connection	Screw connection

Equipment

Lighting	for lighting and monitoring circuit
----------	-------------------------------------

Heating switch	No
Use cases	
Application	Light control
Safety	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK05
Identification	
Application, usage	HVAC control, Light control
Main design line	Light control
Instructions	
Information text	<p>spreader claws, insulated to the supporting ring, self-resetting ; Only suitable in combination with rockers with "0" imprint.</p>