



303303

## On/off switch 3pole 16A/400V

### Technical characteristics

#### Architecture

Type of control unit single rocker

#### Configuration

Switch mode 3-pole off ; with predefined neutral position

Antibacterial treatment No

#### Compatibility

IFTTT support available No

#### Controls and indicators

Push-buttons No

#### Main electrical features

Nominal voltage 400 V

Rated voltage 400 V AC

#### Electric current

Switching current 16 A

#### Dimensions

Depth 42 mm

Insertion depth 31 mm

Height 71 mm

Width 71 mm

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with screw terminals

Type of connection Screw connection

#### Equipment

Lighting for lighting and monitoring circuit

Heating switch No

#### Use cases

Application Light control

**Safety**

---

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK05

---

**Identification**

---

Application, usage	HVAC control ; Light control
Main design line	Light control

---

**Instructions**

---

Information text	spreader claws, insulated to the supporting ring, self-resetting ; Only suitable in combination with rockers with "0" imprint.
------------------	--

---