



303501



## Series switch, round supporting ring, light control

### Technical characteristics

#### Functions

Switching angle	3.5 °
-----------------	-------

#### Configuration

Switch mode	series
Antibacterial treatment	No

#### Compatibility

IFTTT support available	No
-------------------------	----

#### Main electrical features

Nominal voltage	250 V
-----------------	-------

#### Electric current

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

#### Dimensions

Depth	41.6 mm
Height	70.8 mm
Width	70.8 mm

#### Materials

Surface appearance	other
--------------------	-------

#### Connection

Type of connection	Quickconnect
--------------------	--------------

#### Equipment

Heating switch	No
----------------	----

#### Use cases

Application	Light control
-------------	---------------

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07

#### Identification

Main design line	Light control
------------------	---------------