


303601



## Change-over switch, round supporting ring, light control

### Technical characteristics

#### Architecture

Fixing mode flush-mounting

#### Functions

Switching angle 3.5 °

#### Configuration

Switch mode Change-over

Antibacterial treatment No

#### Compatibility

IFTTT support available No

#### Main electrical features

Nominal voltage 250 V

#### Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

#### Dimensions

Depth 41.6 mm

Insertion depth 31 mm

Height 70.8 mm

Width 70.8 mm

#### Materials

Material Plastic/metal

Surface appearance other

#### Connection

Type of connection Plug-in connection

#### Equipment

Heating switch No

#### Use cases

Application Light control

#### Safety

Protection index IP IP20

Impact strength IK07

