



303701

Intermediate switch, round supporting ring, light control

Technical characteristics

Architecture

Fixing mode flush-mounting

Functions

Switching angle 3.5 °

Configuration

Switch mode intermediate

Antibacterial treatment No

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

Dimensions

Depth 41.6 mm

Insertion depth 31 mm

Height 70.8 mm

Width 70.8 mm

Materials

Material Plastic/metal

Surface appearance other

Connection

Type of connection Plug-in connection

Equipment

Heating switch No

Use cases

Application Light control

Safety

Protection index IP IP20

Impact strength IK07

