



303701

Intermediate switch, round supporting ring, light control

Technical characteristics

Functions

Switching angle	3.5 °
-----------------	-------

Configuration

Switch mode	intermediate
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
-----------------	-------

Electric current

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

Dimensions

Depth	41.6 mm
Insertion depth	31 mm
Height	70.8 mm
Width	70.8 mm

Materials

Surface appearance	other
--------------------	-------

Connection

Type of connection	Plug-in connection
--------------------	--------------------

Equipment

Heating switch	No
----------------	----

Use cases

Application	Light control
-------------	---------------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Identification

Main design line	Light control
------------------	---------------