



30653515

Blind switch insert 1p rocker 2g+impr.ed symb.arrow surf./flush-mtd,W.1,gre m LT

Technical characteristics

Architecture

Fixing mode flush-mounting or surface-mounting

Configuration

Switch mode with mechanical and electrical interlock to prevent mutual switch-on

Main electrical features

Rated voltage 250 V AC

Electric current

Switching current 10 A

Connection

Type of connection with plug-in terminals

Cable

Wire with cable entry at top and bottom

Safety

Protection index IP IP55

Use conditions

Operating temperature -40...30 °C

Storage/transport temperature -50...50 °C

Identification

Application, usage Surface-mounted wet-room installation

Main design line Berker W.1

Instructions

Special note text Inserts will only reach the degree of protection IP55 if mounted with a housing surface mounted or frame for flush-mounted installation.

Information text Pins of quick-release lock made of ZAMAK