



30753505

Switch surface-mtd, W.1, grey/light grey matt LT

Technical characteristics

Configuration

Hollow base ample room for wiring under the bases of the inserts

Main electrical features

Rated voltage 250 V AC

Electric current

Switching current 10 AX

Dimensions

Depth 61.5 mm

Height 76 mm

Width 76 mm

Connection

Terminal with Wago clip-in 2-wire connection terminal for wiring ; with two clip-in places for Wago 2-wire connection terminals in the housing floor

Type of connection with plug-in terminals

Cable

Wire with one entry for 2 cables and one entry for cable and tube

Equipment

Sealing with full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Use conditions

Operating temperature -40...30 °C

Storage/transport temperature -50...50 °C

Identification

Application, usage Surface-mounted wet-room installation

Main design line Berker W.1

Instructions

Information text Pins of quick-release lock made of ZAMAK