



30763502

Change-over switch surface-mtd, W.1, p. white, matt, plastic LT

Technical characteristics

Configuration

Hollow base	ample room for wiring under the bases of the inserts
-------------	--

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

Electric current

Switching current	10 AX
-------------------	-------

Dimensions

Depth	61.5 mm
Height	76 mm
Width	76 mm

Connection

Terminal	with two clip-in places for Wago 2-wire connection terminals in the housing floor, with Wago clip-in 2-wire connection terminal for wiring
Type of connection	with plug-in terminals

Cable

Wire	with one entry for 2 cables and one entry for cable and tube
------	--

Equipment

Sealing	with full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside
---------	---

Safety

Protection index IP	IP55
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-40...30 °C
Storage/transport temperature	-50...50 °C

Identification

Application, usage	Surface-mounted wet-room installation
Main design line	Berker W.1

