



32713502

Key switch impr. surf.-mtd,isolated input ,lock-differing lockings,W1

Technical characteristics

Main electrical features

Rated voltage 240 V AC

Electric current

Switching current 10 A

Dimensions

Width 76 mm

Materials

Colour polarwhite

RAL colour RAL 9010 - Pure white

Installation, mounting

Installation mode for screw fastening

Connection

Terminal with two clip-in places for Wago 2-wire connection terminals in the housing floor ; with Wago clip-in 2-wire connection terminal for wiring

Type of connection with screw terminals

Cable

Wire with one entry for 2 cables and one entry for cable and tube

Equipment

Sealing with full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

Closures / Key systems for master-key systems

Use

Differentiation characteristic 2 - Sales Lock - identical lockings

Differentiation characteristic 3 - Sales Key can be removed in 2 positions

Safety

Protection index IP IP55

REACH conform Yes

RoHS conform Yes

Key with 2 keys

Use conditions

Operating temperature -40...30 °C

Storage/transport temperature

-50...50 °C

Identification

Main design line

Berker W.1

Instructions

Information text

Pins of quick-release lock made of ZAMAK