



32713505

## Key switch impr. surf.-mtd,isolated input ,lock-differing lockings,W1

### Technical characteristics

#### Main electrical features

Rated voltage	240 V AC
---------------	----------

#### Electric current

Switching current	10 A
-------------------	------

#### Dimensions

Width	76 mm
-------	-------

#### Installation, mounting

Installation mode	for screw fastening
-------------------	---------------------

#### Connection

Terminal	with two clip-in places for Wago 2-wire connection terminals in the housing floor ; with Wago clip-in 2-wire connection terminal for wiring
----------	---

Type of connection	with screw terminals
--------------------	----------------------

#### Cable

Wire	with one entry for 2 cables and one entry for cable and tube
------	--

#### Equipment

Sealing	with full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside
---------	---

Closures / Key systems	for master-key systems
------------------------	------------------------

#### Use

Differentiation characteristic 2 - Sales	Lock - identical lockings
--	---------------------------

Differentiation characteristic 3 - Sales	Key can be removed in 2 positions
--	-----------------------------------

#### Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Key	with 2 keys
-----	-------------

#### Use conditions

Operating temperature	-40...30 °C
-----------------------	-------------

Storage/transport temperature	-50...50 °C
-------------------------------	-------------

#### Identification

Main design line	Berker W.1
------------------	------------

#### Instructions

Subject to technical modifications

