



32713505

**Key switch impr. surf.-mtd,isolated input ,lock-differing lockings,W1**

**Technical characteristics**

**Main electrical features**

Rated voltage 240 V AC

**Electric current**

Switching current 10 A

**Dimensions**

Width 76 mm

**Materials**

Colour iron grey

RAL colour RAL 7011 - Iron grey

**Installation, mounting**

Installation mode for screw fastening

**Connection**

Terminal with two clip-in places for Wago 2-wire connection terminals in the housing floor ; with Wago clip-in 2-wire connection terminal for wiring

Type of connection with screw terminals

**Cable**

Wire with one entry for 2 cables and one entry for cable and tube

**Equipment**

Sealing with full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

Closures / Key systems for master-key systems

**Use**

Differentiation characteristic 2 - Sales Lock - identical lockings

Differentiation characteristic 3 - Sales Key can be removed in 2 positions

**Safety**

Protection index IP IP55

REACH conform Yes

RoHS conform Yes

Key with 2 keys

**Use conditions**

Operating temperature -40...30 °C

Storage/transport temperature

-50...50 °C

**Identification**

---

Main design line

Berker W.1

**Instructions**

---

Information text

Pins of quick-release lock made of ZAMAK