



32723515

**Key switch f.blinds impr. surf.-mtd,isolated input ,lock-differing lockings,W1**

**Technical characteristics**

**Functions**

Function with push lock function

**Main electrical features**

Rated voltage 250 V AC

**Electric current**

Switching current 10 A

**Dimensions**

Width 76 mm

**Materials**

Colour iron grey

RAL colour RAL 7011 - Iron grey

**Installation, mounting**

Installation mode for screw fastening

**Connection**

Terminal with two clip-in places for Wago 2-wire connection terminals in the housing floor ; isolated input terminals for UP and DOWN ; with Wago clip-in 2-wire connection terminal for wiring

Type of connection with screw terminals

**Cable**

Wire with one entry for 2 cables and one entry for cable and tube

**Equipment**

Sealing with full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

Closures / Key systems for e. g. garage doors

**Use**

Differentiation characteristic 2 - Sales Lock - identical lockings

Differentiation characteristic 3 - Sales Key can be removed in 3 positions

**Safety**

Protection index IP IP55

Key with 2 keys

**Use conditions**

Operating temperature	-40...30 °C
Storage/transport temperature	-50...50 °C
<b>Identification</b>	
Main design line	Berker W.1
<b>Instructions</b>	
Information text	Pins of quick-release lock made of ZAMAK