



3315322045

**3 x Cinch/S-Video soc. out., R.1/R.3, black glossy**

**Technical characteristics**

**Connectivity**

Outlet	with straight outlet
Connectors / jacks	2 cinch double jacks for audio connection (red, white) ; S-Video double jack ; 1 cinch double jack for video connection (yellow)

**Frequency**

Frequency range audio	20 Hz...20 kHz
Frequency range video	max. 160 MHz

**Materials**

Colour of labelling	217,217,217
Colour of design line	black
Colour	black
RAL colour	RAL 9005 - Jet black
Material	Plastic/metal
Material for printing	PC-PMA black
Surface appearance	glossy
Material / surface	gold-plated contacts

**Installation, mounting**

Installation mode	without spreader claws ; for screw fastening
-------------------	--

**Settings**

Shading parameter	R1_czarny
Laser parameter	R1_schwarz

**Equipment**

Type of configuration	Laserdruck
Supporting plate / Supporting ring	with supporting ring

**Identification**

Application, usage	Communication technology
Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	Berker R.1 ; Berker R.3 ; Berker R.8

**Instructions**

Information text	Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; for connecting analogue audio and video devices such as receivers, hi-fi systems and DVD players. ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092
------------------	---