



3315327004

**3 x Cinch/S-Video soc. out., K.5, stainless steel matt, lacq.**

**Technical characteristics**

**Connectivity**

Outlet	with straight outlet
Connectors / jacks	2 cinch double jacks for audio connection (red, white), S-Video double jack, 1 cinch double jack for video connection (yellow)

**Frequency**

Frequency range audio	20 Hz...20 kHz
Frequency range video	max. 160 MHz

**Materials**

Colour of design line	stainless steel
Colour	stainless steel
RAL colour	RAL 9022 - Pearl light grey
Material / workmanship	lacquered
Material	Plastic/metal
Surface appearance	matt
Material / surface	gold-plated contacts

**Installation, mounting**

Installation mode	without spreader claws, for screw fastening
-------------------	---

**Equipment**

Supporting plate / Supporting ring	with supporting ring
------------------------------------	----------------------

**Identification**

Application, usage	Communication technology
Main design line	Berker K.5

**Instructions**

Information text	Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; for connecting analogue audio and video devices such as receivers, hi-fi systems and DVD players. ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092
------------------	---