



3315391909

USB socket outlet

Technical characteristics

Connectivity

Outlet	with straight outlet
Connectors / jacks	USB, double socket type A, USB 2.0 compliant, double jack gold-plated 3.5 mm, stereo

Dimensions

Insertion depth	24.9 mm
-----------------	---------

Frequency

Frequency range audio	20 Hz...20 kHz
-----------------------	----------------

Storage

USB transmission rate	max. 480 Mbit/s
-----------------------	-----------------

Materials

Colour of design line	polar white
Colour	polarwhite
RAL colour	RAL 9010 - Pure white
Material	Plastic/metal
Surface appearance	matt

Installation, mounting

Installation mode	without spreader claws, for screw fastening
-------------------	---

Identification

Application, usage	Communication technology
Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7

Instructions

Information text	<p>Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For connecting mobile devices, such as mobile phones or MP3 players (mini audio), digital cameras and computer peripherals (USB 2.0). ; Observe the instructions of the cable and device manufacturers for maximum USB cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092</p>
------------------	--