



3315391909

USB socket outlet

Technical characteristics

Connectivity

| | |
|--------------------|--|
| Outlet | with straight outlet |
| Connectors / jacks | USB, double socket type A, USB 2.0 compliant ; double jack gold-plated 3.5 mm, stereo |

Dimensions

| | |
|-----------------|---------|
| Insertion depth | 24.9 mm |
|-----------------|---------|

Frequency

| | |
|-----------------------|----------------|
| Frequency range audio | 20 Hz...20 kHz |
|-----------------------|----------------|

Storage

| | |
|-----------------------|-----------------|
| USB transmission rate | max. 480 Mbit/s |
|-----------------------|-----------------|

Materials

| | |
|-----------------------|-----------------------|
| Colour of design line | polar white |
| RAL colour | RAL 9010 - Pure white |
| Surface appearance | matt |

Installation, mounting

| | |
|-------------------|--|
| Installation mode | without spreader claws ; for screw fastening |
|-------------------|--|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |

Identification

| | |
|--------------------------|--------------------------------------|
| Application, usage | Communication technology |
| Secondary design line(s) | Berker S.1 ; Berker B.3 ; Berker B.7 |

Instructions

| | |
|------------------|---|
| Information text | Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For connecting mobile devices, such as mobile phones or MP3 players (mini audio), digital cameras and computer peripherals (USB 2.0). ; Observe the instructions of the cable and device manufacturers for maximum USB cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092 |
|------------------|---|