



3315392045

USB/3.5 mm audio soc. out., R.1/R.3, black glossy

Technical characteristics

Connectivity

| | |
|--------------------|---|
| Outlet | with straight outlet |
| Connectors / jacks | USB, double socket type A, USB 2.0 compliant, double jack gold-plated 3.5 mm, stereo |

Dimensions

| | |
|-----------------|---------|
| Insertion depth | 24.9 mm |
|-----------------|---------|

Frequency

| | |
|-----------------------|----------------|
| Frequency range audio | 20 Hz...20 kHz |
|-----------------------|----------------|

Storage

| | |
|-----------------------|-----------------|
| USB transmission rate | max. 480 Mbit/s |
|-----------------------|-----------------|

Materials

| | |
|-----------------------|----------------------|
| Colour of labelling | 217,217,217 |
| Colour of design line | black |
| Colour | black |
| RAL colour | RAL 9005 - Jet black |
| Material | Plastic/metal |
| Material for printing | PC-PMA black |

Installation, mounting

| | |
|-------------------|---|
| Installation mode | without spreader claws, for screw fastening |
|-------------------|---|

Settings

| | |
|-------------------|------------|
| Shading parameter | R1_czarny |
| Laser parameter | R1_schwarz |

Equipment

| | |
|-----------------------|------------|
| Type of configuration | Laserdruck |
|-----------------------|------------|

Identification

| | |
|--------------------------|------------------------------------|
| Application, usage | Communication technology |
| Main design line | Berker R.1/R.3/R.8 |
| Secondary design line(s) | Berker R.1, Berker R.3, Berker R.8 |

Instructions

Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For connecting mobile devices, such as mobile phones or MP3 players (mini audio), digital cameras and computer peripherals (USB 2.0). ; Observe the instructions of the cable and device manufacturers for maximum USB cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092

Information text