



3315392089

## USB/3.5 mm audio soc. out., R.1/R.3, p. white glossy

### Technical characteristics

#### Connectivity

Outlet	with straight outlet
Connectors / jacks	USB, double socket type A, USB 2.0 compliant ; double jack gold-plated 3.5 mm, stereo

#### Dimensions

Insertion depth	24.9 mm
-----------------	---------

#### Frequency

Frequency range audio	20 Hz...20 kHz
-----------------------	----------------

#### Storage

USB transmission rate	max. 480 Mbit/s
-----------------------	-----------------

#### Materials

Colour of labelling	105,105,105
Colour of design line	polar white
RAL colour	RAL 9010 - Pure white
Material for printing	ASA polar white
Surface appearance	glossy

#### Installation, mounting

Installation mode	without spreader claws ; for screw fastening
-------------------	--

#### Settings

Shading parameter	R1_biały
Laser parameter	R1_weiß

#### Equipment

Type of configuration	Laserdruck
-----------------------	------------

#### Identification

Application, usage	Communication technology
Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	Berker R.1 ; Berker R.3 ; Berker R.8

#### Instructions

Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For connecting mobile devices, such as mobile phones or MP3 players (mini audio), digital cameras and computer peripherals (USB 2.0). ; Observe the instructions of the cable and device manufacturers for maximum USB cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092

Information text