



USB/3.5 mm audio socket outlet, Q.1/Q.3, aluminium velvety, lacquered

Technical characteristics

Connectivity	
Outlet	with straight outlet
Connectors / jacks	USB, double socket type A, USB 2.0 compliant ; double jack gold-plated 3.5 mm, stered
Dimensions	
Insertion depth	24.9 mm
Frequency	
Frequency range audio	20 Hz20 kHz
Storage	
USB transmission rate	max. 480 Mbit/s
Materials	
Colour of design line	aluminium
Surface appearance	velvety
Installation, mounting	
Installation mode	without spreader claws
Identification	
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
Instructions	
	Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74; For connecting mobile devices, such as mobile phones or MP3 players (mini audio), digital cameras and computer peripherals (USB 2.0).; Observe the instructions of the cable and device manufacturers for maximum

USB cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092

Information text