



USB/3.5 mm audio soc. out., Q.1/Q.3, ant. velvety, lacq.

Technical characteristics

Connectivity	
Outlet	with straight outlet
	USB, double socket type A, USB 2.0 compliant;

Connectors / jacks	USB, double socket type A, USB 2.0 compliant ; double jack gold-plated 3.5 mm, stereo
Dimensions	
Insertion depth	24.9 mm
Frequency	
Frequency range audio	20 Hz20 kHz
Storage	
USB transmission rate	max, 480 Mhit/s

Colour of design line	anthracite
Material / workmanship	lacquered
Surface appearance	velvety

Installation mode	without spreader claws ; for screw fastening
Identification	
Application, usage	Communication technology
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9

Instructions	
	Installation recommendation: Kaiser: "Electronic
	box" for compliance with the permissible bending
	radii, Art. No. 1068-02 or 9062-74 ; For connecting
	mobile devices, such as mobile phones or MP3
	players (mini audio), digital cameras and computer
	peripherals (USB 2.0).; Observe the instructions of
	the cable and device manufacturers for maximum
	USB cable lengths! ; Fränkische: "Multimedia tube"

 $\begin{array}{c} \text{for laying pre-assembled connection cable, Art. no.} \\ \text{Information text} \\ \text{294.10.092} \end{array}$