



3315407006

VGA soc. out., K.1, ant. matt, lacq.

Technical characteristics

Connectivity

Outlet	with straight outlet
Plug type	S-VGA compatible
Connectors / jacks	with 15pole D-subminiature jack (front)

Dimensions

Insertion depth	12 mm
-----------------	-------

Frequency

Frequency range video	max. 160 MHz
-----------------------	--------------

Screen

Resolution	max. 1280 x 1024 px
------------	---------------------

Materials

Colour of design line	anthracite
Material / workmanship	lacquered
Surface appearance	matt

Installation, mounting

Installation mode	without spreader claws ; for screw fastening
-------------------	--

Connection

Type of connection	with backside jack for connecting to pre-assembled VGA cable
Connection	with 15pole D-subminiature double jack

Equipment

Supporting plate / Supporting ring	with supporting ring
------------------------------------	----------------------

Safety

REACH conform	Yes
RoHS conform	Yes

Identification

Application, usage	Communication technology
Main design line	Berker K.1

Instructions

Information text

For connecting PCs, notebooks, etc. to display devices such as monitors (including LCD monitors) and projectors. ; Observe the instructions of the cable and device manufacturers for maximum VGA cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092 ; Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74