



3315417006

**VGA soc. out., screw-in lift terminals, K.1, ant. matt, lacq.**

**Technical characteristics**

**Connectivity**

Outlet	with straight outlet
Plug type	S-VGA compatible
Connectors / jacks	with 15pole D-subminiature jack (front)

**Frequency**

Frequency range video	max. 160 MHz
-----------------------	--------------

**Screen**

Resolution	max. 1280 x 1024 px
------------	---------------------

**Materials**

Colour of design line	anthracite
Material / workmanship	lacquered
Surface appearance	matt

**Installation, mounting**

Installation mode	without spreader claws ; for screw fastening
-------------------	--

**Connection**

Conductor cross-section	max. 1.5 mm <sup>2</sup>
Type of connection	with screw-in lift terminals for connection to 15-core VGA cable

**Equipment**

Supporting plate / Supporting ring	with supporting ring
------------------------------------	----------------------

**Use**

Differentiation characteristic 3 - Sales	with screw-in lift terminals
--	------------------------------

**Safety**

REACH conform	Yes
RoHS conform	Yes

**Identification**

Application, usage	Communication technology
Main design line	Berker K.1

**Instructions**

Information text

For connecting PCs, notebooks, etc. to display devices such as monitors (including LCD monitors) and projectors. ; Observe the instructions of the cable and device manufacturers for maximum VGA cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092 ; Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74