



3315418989

**VGA soc. out., screw-in lift terminals, S.1/B.3/B.7, p. white glossy**

**Technical characteristics**

**Connectivity**

|                    |   |
|--------------------|---|
| Outlet             | with straight outlet                    |
| Plug type          | S-VGA compatible                        |
| Connectors / jacks | with 15pole D-subminiature jack (front) |

**Frequency**

|                       |              |
|-----------------------|--------------|
| Frequency range video | max. 160 MHz |
|-----------------------|--------------|

**Screen**

|            |                     |
|------------|---------------------|
| Resolution | max. 1280 x 1024 px |
|------------|---------------------|

**Materials**

|                       |                       |
|-----------------------|-----------------------|
| Colour of design line | polar white           |
| Colour                | polarwhite            |
| RAL colour            | RAL 9010 - Pure white |
| Material              | Plastic/metal         |

**Installation, mounting**

|                   |   |
|-------------------|---|
| Installation mode | without spreader claws, for screw fastening |
|-------------------|---|

**Connection**

|                         |  |
|-------------------------|--|
| Conductor cross-section | max. 1.5 mm <sup>2</sup>   |
| Type of connection      | with screw-in lift terminals for connection to 15-core VGA cable |

**Equipment**

|                                    |                      |
|------------------------------------|----------------------|
| Supporting plate / Supporting ring | with supporting ring |
|------------------------------------|----------------------|

**Use**

|  |                              |
|--|------------------------------|
| Differentiation characteristic 3 - Sales | with screw-in lift terminals |
|--|------------------------------|

**Identification**

|                          |                                    |
|--------------------------|------------------------------------|
| Application, usage       | Communication technology           |
| Main design line         | Berker S.1/B.3/B.7                 |
| Secondary design line(s) | Berker S.1, Berker B.3, Berker B.7 |

**Instructions**

Information text

For connecting PCs, notebooks, etc. to display devices such as monitors (including LCD monitors) and projectors. ; Observe the instructions of the cable and device manufacturers for maximum VGA cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092 ; Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74