



3315422045

## High definition soc. out., R.1/R.3, black glossy

### Technical characteristics

#### Architecture

Number of poles 19pole

#### Connectivity

Outlet with straight outlet

Connectors / jacks with HDMI double socket, type A, supports HDMI technology (V 2.1)

#### Dimensions

Insertion depth 16.8 mm

#### Frequency

Frequency range (vertical) 50...85 Hz

#### Screen

Resolution max. 1920 x 1080 px

#### Storage

Transmission rate max. 8.16 Gbit/s

#### Materials

Colour of labelling 217,217,217

Colour of design line black

Colour black

RAL colour RAL 9005 - Jet black

Material Plastic/metal

Material for printing PC-PMA black

Material / surface gold-plated contacts

#### Installation, mounting

Installation mode without spreader claws, for screw fastening

#### Settings

Shading parameter R1\_czarny

Laser parameter R1\_schwarz

#### Equipment

Type of configuration Laserdruck

#### Identification

Application, usage Communication technology

Main design line Berker R.1/R.3/R.8

**Instructions**

---

Information text

Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For the connection of digital devices for transmission of high-resolution audio and video signals, such as satellite receivers and DVD players, to LCD or plasma screens. ; Observe the instructions of the cable and device manufacturers for maximum HDMI cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092