



3315422089

High definition soc. out., R.1/R.3, p. white glossy

Technical characteristics

Architecture

Number of poles 19pole

Connectivity

Outlet with straight outlet

Connectors / jacks with HDMI double socket, type A, supports HDMI technology (V 2.1)

Dimensions

Insertion depth 16.8 mm

Frequency

Frequency range (vertical) 50...85 Hz

Screen

Resolution max. 1920 x 1080 px

Storage

Transmission rate max. 8.16 Gbit/s

Materials

Colour of labelling 105,105,105

Colour of design line polar white

RAL colour RAL 9010 - Pure white

Material for printing ASA polar white

Surface appearance glossy

Material / surface gold-plated contacts

Installation, mounting

Installation mode without spreader claws ; for screw fastening

Settings

Shading parameter R1_biały

Laser parameter R1_weiß

Equipment

Type of configuration Laserdruck

Safety

REACH conform Yes

RoHS conform Yes

Identification

| | |
|--------------------------|--------------------------------------|
| Application, usage | Communication technology |
| Main design line | Berker R.1/R.3/R.8 |
| Secondary design line(s) | Berker R.1 ; Berker R.3 ; Berker R.8 |

Instructions

| | |
|------------------|--|
| Information text | Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For the connection of digital devices for transmission of high-resolution audio and video signals, such as satellite receivers and DVD players, to LCD or plasma screens. ; Observe the instructions of the cable and device manufacturers for maximum HDMI cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092 |
|------------------|--|