



3315426084

## High definition socket outlet Q.x alu velvety, lacquered

### Technical characteristics

#### Architecture

Number of poles	19pole
-----------------	--------

#### Connectivity

Outlet	with straight outlet
--------	----------------------

Connectors / jacks	with HDMI double socket, type A, supports HDMI technology (V 2.1)
--------------------	---

#### Dimensions

Insertion depth	16.8 mm
-----------------	---------

#### Frequency

Frequency range (vertical)	50...85 Hz
----------------------------	------------

#### Screen

Resolution	max. 1920 x 1080 px
------------	---------------------

#### Storage

Transmission rate	max. 8.16 Gbit/s
-------------------	------------------

#### Materials

Colour of design line	aluminium
-----------------------	-----------

Surface appearance	velvety
--------------------	---------

Material / surface	gold-plated contacts
--------------------	----------------------

#### Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

#### Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

#### Identification

Main design line	Berker Q.1/Q.3/Q.7/Q.9
------------------	------------------------

Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
--------------------------	---

#### Instructions

Information text

Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For the connection of digital devices for transmission of high-resolution audio and video signals, such as satellite receivers and DVD players, to LCD or plasma screens. ; Observe the instructions of the cable and device manufacturers for maximum HDMI cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092