



3315436086

**High definition soc. out. 90° plug connection, Q.x, ant. velvety, lacq.**

#### Technical characteristics

##### Architecture

Number of poles	19pole
-----------------	--------

##### Connectivity

Outlet	with straight outlet
--------	----------------------

Connectors / jacks	with HDMI double socket, type A, supports HDMI technology (V 2.1)
--------------------	---

##### Dimensions

Insertion depth	41 mm
-----------------	-------

##### Frequency

Frequency range (vertical)	50...85 Hz
----------------------------	------------

##### Screen

Resolution	max. 1920 x 1080 px
------------	---------------------

##### Storage

Transmission rate	max. 8.16 Gbit/s
-------------------	------------------

##### Materials

Colour of design line	anthracite
-----------------------	------------

Material / workmanship	lacquered
------------------------	-----------

Material / surface	gold-plated contacts
--------------------	----------------------

##### Installation, mounting

Installation mode	without spreader claws ; for screw fastening
-------------------	--

##### Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

##### Identification

Application, usage	Communication technology
--------------------	--------------------------

Main design line	Berker Q.1/Q.3/Q.7/Q.9
------------------	------------------------

Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
--------------------------	---

##### Instructions

Information text

Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For the connection of digital devices for transmission of high-resolution audio and video signals, such as satellite receivers and DVD players, to LCD or plasma screens. ; Observe the instructions of the cable and device manufacturers for maximum HDMI cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092