



3315437006

**High definition soc. out. 90° plug connection, K.1, ant. matt, lacq.**

#### Technical characteristics

##### Architecture

Number of poles 19pole

##### Connectivity

Outlet with straight outlet

Connectors / jacks with HDMI double socket, type A, supports HDMI technology (V 2.1)

##### Dimensions

Insertion depth 41 mm

##### Frequency

Frequency range (vertical) 50...85 Hz

##### Screen

Resolution max. 1920 x 1080 px

##### Storage

Transmission rate max. 8.16 Gbit/s

##### Materials

Colour of design line anthracite

Material / workmanship lacquered

Surface appearance matt

Material / surface gold-plated contacts

##### Installation, mounting

Installation mode without spreader claws ; for screw fastening

##### Safety

REACH conform Yes

RoHS conform Yes

##### Identification

Application, usage Communication technology

Main design line Berker K.1

##### Instructions

Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For the connection of digital devices for transmission of high-resolution audio and video signals, such as satellite receivers and DVD players, to LCD or plasma screens. ; Observe the instructions of the cable and device manufacturers for maximum HDMI cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092

Information text