



3315438982

High definition soc. out. 90° plug connection, S.1, white glossy

Technical characteristics

Architecture

Number of poles 19pole

Connectivity

Outlet with straight outlet

Connectors / jacks with HDMI double socket, type A, supports HDMI technology (V 2.1)

Dimensions

Insertion depth 41 mm

Frequency

Frequency range (vertical) 50...85 Hz

Screen

Resolution max. 1920 x 1080 px

Storage

Transmission rate max. 8.16 Gbit/s

Materials

Colour of design line white

Colour white

RAL colour RAL 1013 - Oyster white

Material Plastic/metal

Material / surface gold-plated contacts

Installation, mounting

Installation mode without spreader claws, for screw fastening

Identification

Application, usage Communication technology

Main design line Berker S.1/B.3/B.7

Secondary design line(s) Berker S.1, Berker B.3, Berker B.7

Instructions

Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For the connection of digital devices for transmission of high-resolution audio and video signals, such as satellite receivers and DVD players, to LCD or plasma screens. ; Observe the instructions of the cable and device manufacturers for maximum HDMI cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092

Information text