



38122045

**Rot. switch for blinds 2pole centre plate, rot. knobs, R.classic, black glossy**

**Technical characteristics**

**Architecture**

Type of control unit	Rotative
Fixing mode	flush-mounting

**Functions**

Function	with push lock function
----------	-------------------------

**Configuration**

Switch mode	with neutral position
-------------	-----------------------

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Rated current	10 A

**Electric current**

Switching current	10 A
-------------------	------

**Dimensions**

Depth	58.4 mm
-------	---------

**Materials**

Colour of design line	black
Colour	black
Colour	deep black
RAL colour	RAL 9005 - Jet black
Material	Plastic/metal
Surface appearance	glossy

**Installation, mounting**

Installation mode	for screw fastening
-------------------	---------------------

**Connection**

Type of connection	with screw terminals
--------------------	----------------------

**Use**

Differentiation characteristic 2 - Sales	Rotary knobs
--	--------------

**Safety**

Protection index IP	IP20
---------------------	------

**Identification**

