



382120

Switch f.blinds 1p f.lock cyl.,earth contact,neut. p.,splash-prot. flushmtd IP44

Technical characteristics

Architecture

Type of control unit Key

Functions

Function with push lock function

Configuration

Switch mode 1pole ; with neutral position

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

Dimensions

Depth 40.1 mm

Height 70.8 mm

Width 70.8 mm

Installation, mounting

Installation mode without spreader claws ; for screw fastening

Connection

Type of connection with screw terminals

Equipment

Closures / Key systems for master-key systems

Use cases

Application Blind control

Use

Differentiation characteristic 2 - Sales with earth contact

Differentiation characteristic 3 - Sales with neutral-position

Safety

Protection index IP IP44

Identification

Main design line

Splash-protected flush-mounted IP44

Instructions

Information text

Suitable for water-protected, flush-mounted
installation IP44.