



382120

**Switch f.blinds 1p f.lock cyl.,earth contact,neut. p.,splash-prot. flushmtd IP44**

#### Technical characteristics

##### Architecture

Type of control unit	Key
----------------------	-----

##### Functions

Function	with push lock function
----------	-------------------------

##### Configuration

Switch mode	1pole ; with neutral position
-------------	-------------------------------

##### Compatibility

IFTTT support available	No
-------------------------	----

##### Main electrical features

Nominal voltage	250 V
-----------------	-------

Rated voltage	250 V AC
---------------	----------

##### Electric current

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

##### Dimensions

Depth	40.1 mm
-------	---------

Height	70.8 mm
--------	---------

Width	70.8 mm
-------	---------

##### Installation, mounting

Installation mode	without spreader claws ; for screw fastening
-------------------	--

##### Connection

Type of connection	with screw terminals
--------------------	----------------------

##### Equipment

Closures / Key systems	for master-key systems
------------------------	------------------------

##### Use cases

Application	Blind control
-------------	---------------

##### Use

Differentiation characteristic 2 - Sales	with earth contact
--	--------------------

Differentiation characteristic 3 - Sales	with neutral-position
--	-----------------------

##### Safety

Protection index IP	IP44
---------------------	------

<b>Identification</b>	
Main design line	Splash-protected flush-mounted IP44
<b>Instructions</b>	
Information text	Suitable for water-protected, flush-mounted installation IP44.