



382120

**Switch f.blinds 1p f.lock cyl.,earth contact,neut. p.,splash-prot. flushmtd IP44**

#### Technical characteristics

##### Architecture

Type of control unit	Key
Fixing mode	flush-mounting

##### Functions

Function	with push lock function
----------	-------------------------

##### Configuration

Switch mode	1pole, with neutral position
-------------	------------------------------

##### Compatibility

IFTTT support available	No
-------------------------	----

##### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

##### Electric current

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

##### Dimensions

Depth	40.1 mm
Height	70.8 mm
Width	70.8 mm

##### Materials

Material	Plastic/metal
----------	---------------

##### Installation, mounting

Installation mode	without spreader claws, for screw fastening
-------------------	---

##### Connection

Type of connection	with screw terminals
--------------------	----------------------

##### Equipment

Closures / Key systems	for master-key systems
------------------------	------------------------

##### Use cases

Application	Blind control
-------------	---------------

##### Use

Differentiation characteristic 2 - Sales	with earth contact
--	--------------------

**Safety**

---

Protection index IP

IP44

**Identification**

---

Main design line

Splash-protected flush-mounted IP44

**Instructions**

---

Information text

Suitable for water-protected, flush-mounted  
installation IP44.