



382610

## Change-over switch 2pole for lock cylinders, light control

### Technical characteristics

#### Architecture

Type of control unit Key

#### Configuration

Switch mode 2-pole off/change-over

Antibacterial treatment No

#### Compatibility

IFTTT support available No

#### Controls and indicators

Push-buttons No

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

#### Electric current

Switching current 16 AX (200 W Self Ballasted Lamp (SBL))

#### Dimensions

Depth 40.1 mm

Height 70.8 mm

Width 70.8 mm

#### Materials

Surface appearance matt

#### Installation, mounting

Installation mode without spreader claws ; for screw fastening

#### Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with screw terminals

Type of connection Screw connection

#### Equipment

Lighting without lighting (cannot be illuminated)

Closures / Key systems for master-key systems

Lock cylinder for lock cylinder

Heating switch

No

---

**Use cases**

Application

Blind control ; Light control

---

**Safety**

REACH conform

Yes

RoHS conform

Yes

---

**Identification**

Application, usage

Light control

Main design line

Light control

---

**Instructions**

Information text

for standardised profile half-cylinder lock, 40 mm