



382610

Change-over switch 2pole for lock cylinders, light control

Technical characteristics

Architecture

Type of control unit Key

Configuration

Switch mode 2-pole off/change-over

Antibacterial treatment No

Compatibility

IFTTT support available No

Controls and indicators

Push-buttons No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Switching current 16 AX (200 W Self Ballasted Lamp (SBL))

Dimensions

Depth 40.1 mm

Height 70.8 mm

Width 70.8 mm

Materials

Surface appearance matt

Installation, mounting

Installation mode without spreader claws ; for screw fastening

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with screw terminals

Type of connection Screw connection

Equipment

Lighting without lighting (cannot be illuminated)

Closures / Key systems for master-key systems

Lock cylinder for lock cylinder

Heating switch

No

Use cases

Application

Blind control ; Light control

Safety

REACH conform

Yes

RoHS conform

Yes

Identification

Application, usage

Light control

Main design line

Light control

Instructions

Information text

for standardised profile half-cylinder lock, 40 mm