



383120

Push-b. f.blinds 1p f.lock cylinder, earth contact, splash-prot. flush-mtd IP44

Technical characteristics

Architecture

Type of control unit Key

Configuration

Switch mode 1pole

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 40.1 mm

Insertion depth 30.9 mm

Height 70.8 mm

Width 70.8 mm

Installation, mounting

Installation mode without spreader claws ; for screw fastening

Connection

Type of connection with screw terminals

Equipment

Closures / Key systems for master-key systems

Use cases

Application Blind control

Use

Differentiation characteristic 2 - Sales with earth contact

Safety

Protection index IP IP44

Identification

Main design line Splash-protected flush-mounted IP44

Information text

Suitable for water-protected, flush-mounted
installation IP44.