



3862

Rotary switch 2pole off, light control

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

Switching angle	60 °
-----------------	------

Configuration

Switch mode	2-pole off
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

Dimensions

Depth	46 mm
Contact spacing	> 3 mm
Height	71 mm
Width	71 mm

Materials

Material	Plastic/metal
Surface appearance	other

Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

Connection

Type of connection	with screw terminals
Type of connection	Screw connection

Equipment

Heating switch	No
----------------	----

Use cases

Application	Light control
-------------	---------------

Safety

Protection index IP	IP20
---------------------	------

Identification	
Application, usage	Light control
Main design line	Light control

Instructions	
Information text	Note! The wall box must be mounted at a depth of at least 43 mm.