



3862

## Rotary switch 2pole off, light control

### Technical characteristics

#### Architecture

Fixing mode	flush-mounting
-------------	----------------

#### Functions

Switching angle	60 °
-----------------	------

#### Configuration

Switch mode	2-pole off
Antibacterial treatment	No

#### Compatibility

IFTTT support available	No
-------------------------	----

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

#### Dimensions

Depth	46 mm
Contact spacing	> 3 mm
Height	71 mm
Width	71 mm

#### Materials

Material	Plastic/metal
Surface appearance	other

#### Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

#### Connection

Type of connection	with screw terminals
Type of connection	Screw connection

#### Equipment

Heating switch	No
----------------	----

#### Use cases

Application	Light control
-------------	---------------

#### Safety

Protection index IP	IP20
---------------------	------

---

**Identification**

Application, usage

Light control

Main design line

Light control

---

**Instructions**

Information text

Note! The wall box must be mounted at a depth of at least 43 mm.