



386201

Rotary switch 2pole off, light control

Technical characteristics

Architecture

Fixing mode flush-mounting

Functions

Switching angle 60 °

Configuration

Switch mode 2-pole off

Antibacterial treatment No

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Dimensions

Depth 46 mm

Contact spacing > 3 mm

Height 70.8 mm

Width 70.8 mm

Materials

Material Plastic/metal

Surface appearance other

Installation, mounting

Installation mode without spreader claws

Connection

Type of connection with screw terminals

Type of connection Screw connection

Equipment

Heating switch No

Use cases

Application Light control

Safety

Protection index IP IP20

Identification

Application, usage

Light control

Main design line

Light control

Instructions

Information text

Note! The wall box must be mounted at a depth of at least 43 mm.