



387700

Rot. switch, intermediate, 1930/glass/R.classic

Technical characteristics

Architecture

| | |
|----------------------|------------------|
| Type of control unit | Short thumb-grip |
| Fixing mode | flush-mounting |

Configuration

| | |
|-------------|--------------|
| Switch mode | intermediate |
|-------------|--------------|

Controls and indicators

| | |
|--------------|----|
| Push-buttons | No |
|--------------|----|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V |
| Rated voltage | 250 V AC |

Electric current

| | |
|-------------------|-------|
| Switching current | 10 AX |
|-------------------|-------|

Dimensions

| | |
|--------|-------|
| Depth | 42 mm |
| Height | 71 mm |
| Width | 71 mm |

Materials

| | |
|----------|-------------|
| Material | duroplastic |
|----------|-------------|

Installation, mounting

| | |
|-------------------|---------------------|
| Installation mode | with spreader claws |
|-------------------|---------------------|

Connection

| | |
|--------------------|----------------------|
| Type of connection | with screw terminals |
| Type of connection | Screw connection |

Equipment

| | |
|----------|-------------------|
| Lighting | without neon lamp |
|----------|-------------------|

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

Identification

| | |
|-----------------------|---------------------------|
| Appliance switch type | No |
| Main design line | Serie 1930/Glas/R.classic |

