



395619

Pullcord push-button, change-over contact sep. signal contact, light control

Technical characteristics

Architecture

Type of control unit pull cord

Configuration

Switch mode change-over contact, with separate signal contact

Antibacterial treatment No

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 42 mm

Insertion depth 31.2 mm

Contact spacing > 3 mm

Height 71 mm

Width 71 mm

Length

Long pullcord 14 cm

Materials

Surface appearance matt

Installation, mounting

Installation mode for wall and ceiling mounting ; with spreader claws

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Equipment

Lighting for lighting and monitoring circuit

Use cases

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Identification

Application, usage	Light control
Main design line	Light control

Instructions

Information text	spreader claws, insulated to the supporting ring, self-resetting
------------------	--