



395619

## Pullcord push-button, change-over contact sep. signal contact, light control

### Technical characteristics

#### Architecture

Type of control unit pull cord

#### Configuration

Switch mode change-over contact, with separate signal contact

Antibacterial treatment No

#### Compatibility

IFTTT support available No

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

#### Electric current

Momentary-contact current 10 A

#### Dimensions

Depth 42 mm

Insertion depth 31.2 mm

Contact spacing > 3 mm

Height 71 mm

Width 71 mm

#### Length

Long pullcord 14 cm

#### Materials

Surface appearance matt

#### Installation, mounting

Installation mode for wall and ceiling mounting ; with spreader claws

#### Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

#### Equipment

Lighting for lighting and monitoring circuit

#### Use cases

**Safety**

---

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

**Identification**

---

Application, usage	Light control
Main design line	Light control

**Instructions**

---

Information text	spreader claws, insulated to the supporting ring, self-resetting
------------------	--