



3966

## Pullcord switch off/change-over 10 AX

### Technical characteristics

#### Architecture

Type of control unit pull cord

#### Configuration

Switch mode Off/change-over

Antibacterial treatment No

#### Compatibility

IFTTT support available No

#### Controls and indicators

Push-buttons No

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

#### Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

#### Dimensions

Depth 42 mm

Contact spacing > 3 mm

Height 71 mm

Width 71 mm

#### Length

Long pullcord 14 cm

#### Materials

Surface appearance matt

#### Installation, mounting

Installation mode for wall and ceiling mounting ; with spreader claws

#### Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Type of connection Plug-in connection

#### Equipment

Lighting	for lighting and monitoring circuit
Heating switch	No
<b>Use cases</b>	
Application	Light control
<b>Safety</b>	
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
<b>Identification</b>	
Application, usage	Light control
Appliance switch type	No
Main design line	Light control
<b>Instructions</b>	
Information text	spreader claws, insulated to the supporting ring, self-resetting