



41157009

SCHUKO soc. out., screw-in lift terminals, K.1, p. white glossy

Technical characteristics

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Metallic colour	No

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with screw-in lift terminals

Use

Differentiation characteristic 3 - Sales	with screw-in lift terminals
--	------------------------------

Safety

IK protection code against mechanical impacts	05
Protection index IP	IP20
Protection	without enhanced contact protection
With enhanced contact protection	No

Identification

Main design line	Berker K.1
------------------	------------
