


41238982



**SCHUKO soc. out., enhncd contact prot., screw-in lift terminals, S.1, white gl.**

**Technical characteristics**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

**Cover, door**

Cover Central cover plate

**Materials**

Colour of design line white

Colour white

Colour white

Surface appearance glossy

Metallic colour No

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with screw-in lift terminals

**Use**

Differentiation characteristic 2 - Sales with enhanced touch protection

Differentiation characteristic 3 - Sales Screw-in lift terminals

**Safety**

---

IK protection code against mechanical impacts	02
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	Enhanced contact protection
With enhanced contact protection	Yes

---

**Identification**

---

Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7

---