



41431606

**SCHUKO soc. out., screw-in lift terminals, B.3/B.7, ant., matt**

**Technical characteristics**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Insertion depth	32 mm
-----------------	-------

**Cover, door**

Cover	Central cover plate
-------	---------------------

**Materials**

Colour of design line	anthracite
Colour	anthracite
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material	thermoplastic
Surface appearance	matt

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with screw terminals

**Use**

Differentiation characteristic 3 - Sales	with screw-in lift terminals
--	------------------------------

**Safety**

---

IK protection code against mechanical impacts	05
---	----

---

Protection index IP	IP20
---------------------	------

---

Protection	without enhanced contact protection
------------	-------------------------------------

**Identification**

---

Main design line	Berker S.1/B.3/B.7
------------------	--------------------

---

Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7
--------------------------	------------------------------------